

Chamber Volumes

Based on 4cc gasket etc

CC	1275	1293	1310	1330	1380
		+0.020	+0.040	+0.060	73.5
CR					
7	49.1	49.9	50.6	51.4	53.5
7.5	45.0	45.7	46.4	47.2	49.1
8	41.5	42.2	42.8	43.5	45.3
8.5	38.5	39.1	39.7	40.3	42.0
9	35.8	36.4	36.9	37.6	39.1
9.5	33.5	34.0	34.5	35.1	36.6
10	31.4	31.9	32.4	32.9	34.3
10.5	29.6	30.0	30.5	31.0	32.3
11	27.9	28.3	28.8	29.3	30.5
CC	998	1014	1030	1046	1062
		+0.020	+0.040	+0.060	+0.080
CR					
7.5	34.4	35.0	35.6	36.2	36.8
8	31.6	32.2	32.8	33.4	33.9
8.5	29.3	29.8	30.3	30.9	31.4
9	27.2	27.7	28.2	28.7	29.2
9.5	25.4	25.8	26.3	26.8	27.2
10	23.7	24.2	24.6	25.1	25.5
10.5	22.3	22.7	23.1	23.5	23.9
11	21.0	21.4	21.8	22.2	22.6
CC	1098	1116	1134	1151	1169
		+0.020	+0.040	+0.060	+0.080
CR					
7.5	34.4	35.0	35.6	36.2	36.8
8	31.6	32.2	32.8	33.4	33.9
8.5	29.3	29.8	30.3	30.9	31.4
9	27.2	27.7	28.2	28.7	29.2
9.5	25.4	25.8	26.3	26.8	27.2
10	23.7	24.2	24.6	25.1	25.5
10.5	22.3	22.7	23.1	23.5	23.9
11	21.0	21.4	21.8	22.2	22.6